

EK-402U

Full Screen - 16:10

Resolution: WUXGA (1920x1200)
 Aspect Ratio: (10 High by 16 Wide by 18.868 Diagonal)
 Aperture: 0.568 in. wide

Screen Dimensions.

H'	1.8	2.7	3.5	4.9	6.3	7.5	8.7
W'	2.8	4.2	5.7	7.8	10.0	12.0	14.0
D''	40	60	80	110	142	170	198

EIKI Part No. Ref. T/W Shift/Limits Attached Lens EFL Throw (Distance to Screen) in feet.

EK-402U													
Standard Lens		1.39	20 : -1	Manual, Zoom	0.790	3.9	5.9	7.9	10.8	13.9	16.7	19.5	
		2.09	(fixed)	f:2.4-2.9	1.185	5.9	8.8	11.8	16.2	20.9	25.0	29.2	

EK-401W

Full Screen - 16:10

Resolution: WXGA (1280x800)
 Aspect Ratio: (10 High by 16 Wide by 18.868 Diagonal)
 Aperture: 0.568 in. wide

Screen Dimensions.

H'	1.8	2.7	3.5	4.9	6.3	7.5	8.7
W'	2.8	4.2	5.7	7.8	10.0	12.0	14.0
D''	40	60	80	110	142	170	198

EIKI Part No. Ref. T/W Shift/Limits Attached Lens EFL Throw (Distance to Screen) in feet.

EK-401W													
Standard Lens		1.45	15 : -1	Manual, Zoom	0.822	4.1	6.1	8.2	11.3	14.5	17.4	20.3	
		2.17	(fixed)	f:2.4-2.9	1.235	6.1	9.2	12.3	16.9	21.7	26.1	30.4	

EK-400X

Full Screen - 4:3

Resolution: XGA (1024x768)
 Aspect Ratio: (3 High by 4 Wide by 5 Diagonal)
 Aperture: 0.56 in. wide

Screen Dimensions.

H'	2	3	5	6	7.5	9	10
W'	2.7	4.0	6.67	8.0	10.0	12.0	14
D''	40	60	100	120	150	180	207

EIKI Part No. Ref. T/W Shift/Limits Attached Lens EFL Throw (Distance to Screen) in feet.

EK-400X													
Standard Lens		1.43	9 : -1	Manual, Zoom	0.800	3.8	5.7	9.5	11.4	14.3	17.1	20.0	
		2.14	(fixed)	f:2.4~2.9	1.200	5.7	8.6	14.3	17.1	21.4	25.7	30.0	

How to use the T/W column. If your screen size does not appear on this chart, use the T/W column to find the lens you need. Divide the Throw distance by the screen Width to get your "target T/W number". Then, look for a lens with a T/W range that covers it.

Understanding Shift/Limits. The numbers in the Shift/Limits column express the projector positions possible as a ratio of the image heights Above:Below a line drawn perpendicular to the screen between the lens and the screen. 1:1 = center of the image. The two sides of a ratio are cumulative, so the expression 10:-1.7 means that the bottom of the image starts 1/8.3 of the image height above the imaginary lens center line.

These charts are a simulation. Effective Focal Length (EFL) most accurately represents lens behavior, and drives the calculations.. Calculations are from the front glass of the lens and accurate to approximately +/- 3.5%. Specifications are subject to change without notice.